


Nano-Quick Control Connectors, Female Straight 3 Wire, IDC

By Hubbell Wiring Device-Kellems
Catalog # [NCTS13IDC](#)



Nano-Quick Control Connectors, Female Straight 3 Wire, IDC

Features

- Strain Relief Bushing Protects terminations
- Wire Guide For virtually toolless termination
- Copper Alloy insulation displacement contacts
- Rugged, Nickel-plated Hardware prevents corrosion

Application

Quick Connect/Disconnect Signal and Control

Specifications

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07• UL 2238 and UL50E, File No. E1
EU RoHS Indicator	Yes

Conductor

Conductor Type	Copper
Number Of Conductors	3-Pole

Dimensions

Diameter Live Part	.38"
--------------------	------

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Specifications	<ul style="list-style-type: none">• Contact Materials - Copper Alloy• Contact Plating - Tin over Nickel• Housing - Polyester Elasmomer, Black• Strain Relief Bushing - Neoprene, Black• Wire Guide - Nylon 6/6, Gray
UPC	783585226637
Color	Black

Logistics

Carton Quantity	25
-----------------	----

Operational

Temperature Rating	-20 Deg C to 105 Deg C
--------------------	------------------------

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)