

NCTS3202

By Hubbell Wiring Device-Kellems
Catalog # [NCTS3202](#)

Nano-Quick, Threaded Female Plug, 3P, 2M



Application

Quick Connect/Disconnect Signal and Control

General

Catalog Number	NCTS3202
Color	Black
EU RoHS Indicator	Yes
Insulation	TPE
Item Type	Female Straight Plug
Jacket	TPE
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585956367

Dimensions

Diameter Live Part	.38"
--------------------	------

Conductor Related

Conductor Type	Copper
Number of Conductors	3-Pole

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - NCTS3202 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1648_INSTALLINST](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_NCTS3202_DRAWING_PDF](#)
[Specifications - NCTS3202 Specification Sheet English](#)
[Specifications - NCTS3202 Specification Sheet French](#)