

## Nano-Quick Control Connectors, Male, Straight Plug, 3 Wire, IDC

By Hubbell Wiring Device-Kellems  
Catalog # [NITS13IDC](#)



Nano-Quick Control Connectors, Male, Straight Plug, 3 Wire, IDC

### Features

- Strain Relief Bushing Protects terminations
- Wire Guide For virtually toolless termination
- Copper Alloy insulation displacement contacts
- Rugged, Nickel-plated Hardware prevents corrosion

### Application

Quick Connect/Disconnect Signal and Control

### Specifications

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07</li><li>• UL 2238 and UL50E, File No. E1</li></ul>
EU RoHS Indicator	Yes

### Conductor

Conductor Type	Copper
Number Of Conductors	3-Pole

### Dimensions

Diameter Live Part	.38"
--------------------	------

### General

OEM Brand Name	Hubbell Wiring Device-Kellems
Specifications	<ul style="list-style-type: none"><li>• Contact Materials - Copper Alloy</li><li>• Contact Plating - Tin over Nickel</li><li>• Housing - Polyester Elastomer, Black</li><li>• Strain Relief Bushing - Neoprene, Black</li><li>• Wire Guide - Nylon 6/6, Gray</li></ul>
UPC	783585226620
Color	Black

### Logistics

Carton Quantity	25
-----------------	----

### Operational

Temperature Rating	-20 Deg C to 105 Deg C
--------------------	------------------------

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[Spanish, French, English\]](#)