



Wallplates, Nylon, 1-Gang, 1) 1.60" Opening, Brown

By Bryant
Catalog # [NP720OW](#)

Wallplates, Nylon, 1-Gang, 1) 1.60" Opening, Brown



Features

- Reinforcement ribs for extra strength
- High-impact, self-extinguishing nylon material
- Captive screw feature holds mounting screw in place
- 1-Single 1.60 in. (40.6) Diameter Opening

Application

Protection against contact of live terminals and wiring. Provides finished look to installation.

Specifications

Industry Standard(s)	UL Listed
EU RoHS Indicator	Yes

Configuration

Orientation	Vertical Mount
Number of Gang(s)	1-Gang

Dimensions

Size	Standard
Thickness	0.06

General

Material - Mounting Hardware Type	Screw Mounting Single
Material Specifications	Nylon
	<ul style="list-style-type: none"> • Height - 4.63" (117.6) • Hole Diameter - 1.60 in. (40.6) • Mounting Screw - Steel • Plate Material - Nylon • Size - 1-Gang • Thickness - .06 in. (1.5).

UPC	883778103667
Style	1-Single - 1.60 in. Hole
Color	Office White

Logistics

Carton Quantity	25
-----------------	----