

Marine Wiring Products, Non-Metallic Vaportight Fixture

By Hubbell Wiring Device-Kellems
Catalog # [NVX15GHGA](#)

Marine Wiring Products, Non-Metallic Vaportight Fixture



Features

- High strength protective globe guard
- High temperature silicone gasketing maintains integrity
- Heat resistant glass globe withstands thermal shock in wet locations

Application

Marine Lighting

Specifications

EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Industry Standard(s)	<ul style="list-style-type: none">• UL 1598 Standard• UL1571 Listed• UL595 Listed

Configuration

Ballast/Driver Manufacturer	None
Number of Lamps	1

Current

Amperage Rating	1.2 A
Frequency Rating	50-60 Hz
Wattage	150 W
Voltage Rating	125 VAC

Dimensions

Length	10.4 in
Width	5.2 in
Height	5.3 in
Dimensions	10.4 in x 5.2 in x 5.3 in

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Lamp Included	No
Socket Type	Medium Base
Style	Vapor Tight
Color	Gray
Material - Mounting Hardware	Screw Mounting
Material	Composite
Specifications	<ul style="list-style-type: none">• Material - Thermoplastic Polyester• Product Type - Lighting Fixtures• Version - Ceiling Mount Fixture

Lamp Type	A Lamp
UPC	783585357386

Logistics

Carton Quantity	5
Pallet Quantity	154

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)