

**Signal And Control, Linkosity, Cordset,  
Female, Single End, Straight, 3-Wire, 10A  
600V AC, PB Wire Code, 5' Length,  
Stainless Hex Nuts**



By Hubbell Wiring Device-Kellems  
Catalog # [PF1003PB005S](#)

Signal And Control, Linkosity, Cordset, Female, Single End,  
Straight, 3-Wire, 10A 600V AC, PB Wire Code, 5' Length,  
Stainless Hex Nuts

**Features**

- Linkosity
- Cordset
- Female
- Single End

**Application**

Quick Connect/Disconnect Signal and Control

**Specifications**

EU RoHS Indicator Yes

**Conductor**

Conductor Type Copper  
Strands Multi  
Number Of Conductors 3-Pole

**Current**

Amperage Rating 10 A

Voltage Rating 600V kV

**Dimensions**

Outside Diameter 0.71

**General**

Plug Type Linkosity  
OEM Brand Name Hubbell Wiring Device-Kellems  
UPC 783585243245  
Color Gray

**Logistics**

Carton Quantity 10

**Operational**

Temperature Rating -20 Deg C to 105 Deg C

**Product Assets**

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)