

## Linkosity, Female Cable 10A, 3P, 20'

By Hubbell Wiring Device-Kellems  
Catalog # [PF1003PB020](#)

Linkosity, Female Cable 10A, 3P, 20'



### Features

- Linkosity
- Female Cable 10A
- 3P
- 20'

### Application

Quick Connect/Disconnect Signal and Control

### Specifications

EU RoHS Indicator Yes

### Conductor

Conductor Type Copper  
Strands Multi  
Number Of Conductors 3-Pole

### Current

Amperage Rating 10 A

Voltage Rating 600V kV

### Dimensions

Outside Diameter 0.71

### General

Plug Type Linkosity  
OEM Brand Name Hubbell Wiring Device-Kellems  
UPC 783585116389  
Color Gray

### Logistics

Carton Quantity 5

### Operational

Temperature Rating -20 Deg C to 105 Deg C

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)