

Linkosity, Female Cable, 3W, 60'

By Hubbell Wiring Device-Kellems
Catalog # [PF1003PB060](#)

Linkosity, Female Cable, 3W, 60'



Features

- Linkosity
- Female Cable
- 3W
- 60'

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Strands Multi
Number Of Conductors 3-Pole

Current

Amperage Rating 10 A
Voltage Rating 600V kV

Dimensions

Outside Diameter 0.71

General

Plug Type Linkosity
OEM Brand Name Hubbell Wiring Device-Kellems
UPC 783585524009
Color Gray

Operational

Temperature Rating -20 Deg C to 105 Deg C

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)