

Signal And Control, Linkosity, Cordset,
Female, Single End, Straight, 4-Wire, 10A
600V AC, PA Wire Code, 30' Length

By Hubbell Wiring Device-Kellems
Catalog # [PF1004PA030](#)

Signal And Control, Linkosity, Cordset, Female, Single End,
Straight, 4-Wire, 10A 600V AC, PA Wire Code, 30' Length

Features

- Linkosity
- Cordset
- Female
- Single End

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Number Of Conductors 4-Pole

Dimensions



Diameter Live Part .46"

General

Jacket PVC
OEM Brand Name Hubbell Wiring Device-Kellems
UPC 783585243047
Color Gray

Logistics

Carton Quantity 5

Operational

Temperature Rating -20 Deg C to 105 Deg C

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)