

## Linkosity, Female Cable 10A, 12P, 50'

By Hubbell Wiring Device-Kellems  
Catalog # [PF1012PE050](#)

Linkosity, Female Cable 10A, 12P, 50'



### Features

- Linkosity
- Female Cable 10A
- 12P
- 50'

### Application

Quick Connect/Disconnect Signal and Control

### Specifications

EU RoHS Indicator Yes

### Conductor

Conductor Type Copper  
Strands Multi  
Number Of Conductors 12-Pole

### Current

Amperage Rating 7 A

Voltage Rating 600V kV

### Dimensions

Outside Diameter 0.89

### General

Plug Type Linkosity  
OEM Brand Name Hubbell Wiring Device-Kellems  
UPC 783585116365  
Color Gray

### Logistics

Carton Quantity 10

### Operational

Temperature Rating -20 Deg C to 105 Deg C

### Product Assets

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)