

Signal And Control, Linkosity, Cordset,
Female, Single End, Straight, 4-Wire, 20A
600V AC, PA Wire Code, 50' Length

By Hubbell Wiring Device-Kellems
Catalog # [PF2004PA050](#)

Signal And Control, Linkosity, Cordset, Female, Single End,
Straight, 4-Wire, 20A 600V AC, PA Wire Code, 50' Length

Features

- Linkosity
- Cordset
- Female
- Single End

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Strands Multi
Number Of Conductors 4-Pole

Current

Amperage Rating 20 A
Voltage Rating 600V kV

Dimensions

Outside Diameter 0.75

General

Plug Type Linkosity
OEM Brand Name Hubbell Wiring Device-Kellems
UPC 783585358239
Color Gray

Operational

Temperature Rating -20 Deg C to 105 Deg C

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)

