

Linkosity, Female Cable, 20A Single, 5'

By Hubbell Wiring Device-Kellems
Catalog # [PF2303PB005](#)

Linkosity, Female Cable, 20A Single, 5'



Features

- Linkosity
- Female Cable
- 20A Single
- 5'

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Strands Multi
Number Of Conductors 3-Pole

Current

Amperage Rating 20 A

Voltage Rating 600V kV

Dimensions

Outside Diameter 0.71

General

Plug Type Linkosity
OEM Brand Name Hubbell Wiring Device-Kellems
UPC 783585524221
Color Gray

Logistics

Carton Quantity 5

Operational

Temperature Rating -20 Deg C to 105 Deg C

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)