

LINKOSITY, Right Angle Female Plug, 20A 5-Pole, 10' Length

By Hubbell Wiring Device-Kellems
Catalog # [PG2005PA010](#)

LINKOSITY, Right Angle Female Plug, 20A 5-Pole, 10' Length



Oh No!
IMAGE COMING SOON

Features

- LINKOSITY
- Right Angle Female Plug
- 20A 5-Pole
- 10' Length

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Strands Multi
Number Of Conductors 5-Pole

Current

Amperage Rating 20 A

Voltage Rating 600V kV

Dimensions

Outside Diameter 0.75

General

Plug Type Linkosity
OEM Brand Name Hubbell Wiring Device-Kellems
UPC 783585243115
Color Gray

Logistics

Carton Quantity 10

Operational

Temperature Rating -20 Deg C to 105 Deg C

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)