

LINKOSITY, Female Plug, 6-Pole, 20A SNIG, 1' Length

By Hubbell Wiring Device-Kellems
Catalog # [PG2306PB001](#)

LINKOSITY, Female Plug, 6-Pole, 20A SNIG, 1' Length



Oh No!
IMAGE COMING SOON

Features

- LINKOSITY6-Pole
- 20A SNIG
- 1' Length

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Strands Multi
Number Of Conductors 6-Pole

Current

Amperage Rating 20 A
Voltage Rating 600V kV

Dimensions

Outside Diameter 0.77

General

Plug Type Linkosity
OEM Brand Name Hubbell Wiring Device-Kellems
UPC 783585243191
Color Gray

Logistics

Carton Quantity 20

Operational

Temperature Rating -20 Deg C to 105 Deg C

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)