

Linkosity

30 AMP 2W Double Ended Cable, 5'



Ordering Information

Color	UPC	Catalog Number
Gray	783585504247	PH0302PE005

Specifications

Amperage Rating	30 A
Application	Quick Connect/Disconnect Signal and Control
Conductor Size	#10 AWG
Number of Conductors	2-Pole
Special Features	All Blue Wires
Strands	Multi
Voltage Rating	600V kV
Insulation	PVC
Outside Diameter	0.67
Temperature Rating	-20 Deg C to 105 Deg C



Online Resources

- Customer Sales Drawings
- eCatalog
- Installation Instructions

