

Linkosity
10A, 4W, Double Ended Cable, 50'

HUBBELL

Ordering Information

Color	UPC	Catalog Number
Gray	783585504551	PH1004PA050

Specifications

Amperage Rating	10 A
Application	Quick Connect/Disconnect Signal and Control
Conductor Size	#12 AWG
Number of Conductors	4-Pole
Special Features	Green/Yellow/Black Wires
Strands	Multi
Voltage Rating	600V kV
Insulation	PVC
Outside Diameter	0.75
Temperature Rating	-20 Deg C to 105 Deg C



Online Resources

- Customer Sales Drawings
- eCatalog
- Installation Instructions

