

Linkosity

Double Ended Cable, 10A, 6P, 5'



Ordering Information

Color	UPC	Catalog Number
Gray	783585350172	PH1006PE005

Specifications

Amperage Rating	10 A
Application	Quick Connect/Disconnect Signal and Control
Conductor Size	#12 AWG
Number of Conductors	6-Pole
Special Features	All Blue Wires
Strands	Multi
Voltage Rating	600V kV
Insulation	PVC
Outside Diameter	0.77
Temperature Rating	-20 Deg C to 105 Deg C



Online Resources

- Customer Sales Drawings
- eCatalog
- Installation Instructions

