

Linkosity
Double Ended Cable, 20A

HUBBELL

Ordering Information

| | | |
|----------------------|----------------------------|--------------------------------------|
| Color Gray | UPC 783585504841 | Catalog Number PH2004PB020 |
|----------------------|----------------------------|--------------------------------------|

Specifications

| | |
|----------------------|---|
| Amperage Rating | 20 A |
| Application | Quick Connect/Disconnect Signal and Control |
| Conductor Size | #12 AWG |
| Number of Conductors | 4-Pole |
| Special Features | Green/Yellow/White/Black Wires |
| Strands | Multi |
| Voltage Rating | 600V kV |
| Insulation | PVC |
| Outside Diameter | 0.75 |
| Temperature Rating | -20 Deg C to 105 Deg C |



Online Resources

[Customer Sales Drawings](#)
[eCatalog](#)
[Installation Instructions](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

