

Linkosity

Cordset, Male/Female, Double End, Straight, 5-Wire, 10A  
600V AC, PA Wire Code, 40' Length

HUBBELL

Ordering Information

|       |              |                |
|-------|--------------|----------------|
| Color | UPC          | Catalog Number |
| Gray  | 783585524603 | PH2005PA040    |

Specifications

|                      |                                             |
|----------------------|---------------------------------------------|
| Amperage Rating      | 20 A                                        |
| Application          | Quick Connect/Disconnect Signal and Control |
| Conductor Size       | #12 AWG                                     |
| Number of Conductors | 5-Pole                                      |
| Special Features     | Green/Yellow/Black Wires                    |
| Strands              | Multi                                       |
| Voltage Rating       | 600V kV                                     |
| Insulation           | PVC                                         |
| Outside Diameter     | 0.75                                        |
| Temperature Rating   | -20 Deg C to 105 Deg C                      |



Online Resources

- Customer Sales Drawings
- eCatalog
- Installation Instructions

