

Linkosity

Cordset, Male/Female, Double End, Straight, 5-Wire, 10A
600V AC, PB Wire Code, 35' Length

HUBBELL

Ordering Information

Color	UPC	Catalog Number
Gray	783585185125	PH2005PB035

Specifications

Amperage Rating	20 A
Application	Quick Connect/Disconnect Signal and Control
Conductor Size	#12 AWG
Number of Conductors	5-Pole
Special Features	Green/Yellow/White/Black Wires
Strands	Multi
Voltage Rating	600V kV
Insulation	PVC
Outside Diameter	0.75
Temperature Rating	-20 Deg C to 105 Deg C



Online Resources

- Customer Sales Drawings
- eCatalog
- Installation Instructions