

Linkosity

Double Ended Cable, 20A Single, 3-Wire, 5'

HUBBELL

Ordering Information

Color Gray	UPC 783585116198	Catalog Number PH2303PB005
----------------------	----------------------------	--------------------------------------

Specifications

Amperage Rating	20 A
Application	Quick Connect/Disconnect Signal and Control
Conductor Size	#12 AWG, #10 AWG Neutral
Number of Conductors	3-Pole
Special Features	Green/Yellow/White/Black Wires, Super Neutral, Isolated Ground
Strands	Multi
Voltage Rating	600V kV
Insulation	PVC
Outside Diameter	0.71
Temperature Rating	-20 Deg C to 105 Deg C



Online Resources

[Customer Sales Drawings](#)
[eCatalog](#)
[Installation Instructions](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

