

Linkosity

Double Ended Cable, 20A 4P, 2'



Ordering Information

Color	UPC	Catalog Number
Gray	783585350240	PH2304PB002

Specifications

Amperage Rating	20 A
Application	Quick Connect/Disconnect Signal and Control
Conductor Size	#12 AWG, #10 AWG Neutral
Number of Conductors	4-Pole
Special Features	Green/Yellow/White/Black Wires, Super Neutral, Isolated Ground
Strands	Multi
Voltage Rating	600V kV
Insulation	PVC
Outside Diameter	0.75
Temperature Rating	-20 Deg C to 105 Deg C



Online Resources

- Customer Sales Drawings
- eCatalog
- Installation Instructions

