

Linkosity

Double Ended Cable, 4W, 10' Length



Ordering Information

Color	UPC	Catalog Number
Gray	783585504711	PH3004PB010

Specifications

Amperage Rating	30 A
Application	Quick Connect/Disconnect Signal and Control
Conductor Size	#10 AWG
Number of Conductors	4-Pole
Special Features	Green/Yellow/White/Black Wires
Strands	Multi
Voltage Rating	600V kV
Insulation	PVC
Outside Diameter	0.75
Temperature Rating	-20 Deg C to 105 Deg C



Online Resources

- Customer Sales Drawings
- eCatalog
- Installation Instructions

