

Linkosity

Double Ended Cable 3A, 3P, 5'

HUBBELL

Ordering Information

Color	UPC	Catalog Number
Gray	783585505237	PHR303PE005

Specifications

Amperage Rating	30 A
Application	Quick Connect/Disconnect Signal and Control
Conductor Size	#14 AWG
Number of Conductors	3-Pole
Special Features	All Blue Wires
Strands	Multi
Voltage Rating	300V kV
Insulation	PVC
Outside Diameter	0.71
Temperature Rating	-20 Deg C to 105 Deg C



Online Resources

[Customer Sales Drawings](#)
[eCatalog](#)
[Installation Instructions](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

