

Ordering Information

Color	UPC	Catalog Number
Gray	783585505077	PHR303PE010

Specifications

Amperage Rating	30 A
Application	Quick Connect/Disconnect Signal and Control
Conductor Size	#14 AWG
Number of Conductors	3-Pole
Special Features	All Blue Wires
Strands	Multi
Voltage Rating	300V kV
Insulation	PVC
Outside Diameter	0.71
Temperature Rating	-20 Deg C to 105 Deg C



Online Resources

- Customer Sales Drawings
- eCatalog
- Installation Instructions