

Signal And Control, Linkosity, Cordset, Male, Single Ended, Straight, 4-Wire, 10A 600V AC, PA Wire Code, 5 'Length

By Hubbell Wiring Device-Kellems
Catalog # [PM1004PA005](#)

Signal And Control, Linkosity, Cordset, Male, Single Ended, Straight, 4-Wire, 10A 600V AC, PA Wire Code, 5 'Length



Features

- Linkosity
- Cordset
- Male
- Single Ended

Application

Plug Together Power Distribution, No Pass Thru

Specifications

| | |
|--------------------------|-------------------------------------------------|
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| EU RoHS Indicator | Yes |
| Nema Rating | Non-NEMA |

Conductor

| | |
|-----------------|------------------|
| Number Of Wires | 4-Wire Grounding |
| Wire Size | #12 AWG |
| Number Of Poles | 3-Pole |

Current

| | |
|---------------------------|----------------------|
| Phase | Single Phase Control |
| Current / Amperage Rating | 10 A |

| | |
|-----------------|----------------|
| Connectivity | Plug Together |
| Current Rating | 10 A |
| Amperage Rating | 10 A |
| Wattage | 2500 |
| Voltage Rating | 250V AC Max kV |

Dimensions

| | |
|--------------|------------------------|
| Display Size | Standard Sized Product |
|--------------|------------------------|

General

| | |
|------------------------------|-------------------------------|
| Item Type | Conduit Feed Pre-Wired Box |
| Material - Mounting Hardware | Screw Mounting |
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Material | Thermoplastic |
| UPC | 783585185040 |
| Color | Gray |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)