

Signal And Control, Linkosity, Cordset, Male, Single Ended, Straight, 4-Wire, 10A 600V AC, PB Wire Code, 35' Length

By Hubbell Wiring Device-Kellems
Catalog # [PM1004PB035](#)

Signal And Control, Linkosity, Cordset, Male, Single Ended, Straight, 4-Wire, 10A 600V AC, PB Wire Code, 35' Length



Features

- Linkosity
- Cordset
- Male
- Single Ended

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Wet and Damp Locations
EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Number Of Wires	4-Wire Grounding
Wire Size	Pre-Terminated
Number Of Poles	3-Pole

Current

Phase	Single Phase
Current / Amperage Rating	10 A

Connectivity	Pre-Terminated
Current Rating	10 A
Amperage Rating	10 A
Wattage	6000
Voltage Rating	600V AC kV

Dimensions

Display Size	Linkosity
--------------	-----------

General

Item Type	Male Plug
Material - Mounting Hardware	Cord Mounted
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585184982
Color	Gray

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)