

## Signal And Control, Linkosity, Cordset, Male, Single Ended, Straight, 4-Wire, 10A 600V AC, PB Wire Code, 50' Length

By Hubbell Wiring Device-Kellems  
Catalog # [PM1004PB050](#)

Signal And Control, Linkosity, Cordset, Male, Single Ended, Straight, 4-Wire, 10A 600V AC, PB Wire Code, 50' Length



### Features

- Linkosity
- Cordset
- Male
- Single Ended

### Application

Quick Connect/Disconnect Signal and Control

### Specifications

EU RoHS Indicator Yes

### Conductor

Conductor Type Copper  
Strands Multi  
Number Of Conductors 4-Pole

### Current

Amperage Rating 10 A  
Voltage Rating 600V kV

### Dimensions

Outside Diameter 0.75

### General

Plug Type Linkosity  
OEM Brand Name Hubbell Wiring Device-Kellems  
UPC 783585358208  
Color Gray

### Operational

Temperature Rating -20 Deg C to 105 Deg C

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)