

Signal And Control, Linkosity, Cordset,
Male, Single Ended, Straight, 4-Wire, 20A
600V AC, PA Wire Code, 30' Length

By Hubbell Wiring Device-Kellems
Catalog # [PM2004PA030](#)

Signal And Control, Linkosity, Cordset, Male, Single Ended,
Straight, 4-Wire, 20A 600V AC, PA Wire Code, 30' Length

Features

- Linkosity
- Cordset
- Male
- Single Ended

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Strands Multi
Number Of Conductors 4-Pole

Current

Amperage Rating 20 A



Voltage Rating	600V kV
Dimensions	
Outside Diameter	0.75
General	
Plug Type	Linkosity
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585524429
Color	Gray

Logistics	
Carton Quantity	3
Operational	
Temperature Rating	-20 Deg C to 105 Deg C

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)