

Signal And Control, Linkosity, Cordset, Male, Single Ended, Straight, 5-Wire, 20A 600V AC, PA Wire Code, 30' Length

By Hubbell Wiring Device-Kellems
Catalog # [PM2005PA030](#)

Signal And Control, Linkosity, Cordset, Male, Single Ended, Straight, 5-Wire, 20A 600V AC, PA Wire Code, 30' Length

Features

- Linkosity
- Cordset
- Male
- Single Ended

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Strands Multi
Number Of Conductors 5-Pole

Current



Amperage Rating 20 A
Voltage Rating 600V kV

Dimensions

Outside Diameter 0.75

General

Plug Type Linkosity
OEM Brand Name Hubbell Wiring Device-Kellems
UPC 783585358116
Color Gray

Operational

Temperature Rating -20 Deg C to 105 Deg C

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)