

Linkosity, Male Right Angle Cable, 4-Wire, 10A, 5' Cable.

By Hubbell Wiring Device-Kellems
Catalog # [PN1004PB005](#)

Linkosity, Male Right Angle Cable, 4-Wire, 10A, 5' Cable.



Features

- Linkosity
- Male Right Angle Cable
- 4-Wire
- 10A
- 5' Cable.

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Strands Multi
Number Of Conductors 4-Pole

Current

Amperage Rating 10 A

Voltage Rating 600V kV

Dimensions

Outside Diameter 0.75

General

Plug Type Linkosity
OEM Brand Name Hubbell Wiring Device-Kellems
UPC 783585128184
Color Gray

Logistics

Carton Quantity 10

Operational

Temperature Rating -20 Deg C to 105 Deg C

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)