

**Signal And Control, Linkosity, Cordset,
Male, Single Ended 90 Degree, 8-Wire, 10A
600V AC, PE Wire Code, 10' Length,
Stainless Hex Nuts**



By Hubbell Wiring Device-Kellems
Catalog # [PN1008PE010S](#)

Signal And Control, Linkosity, Cordset, Male, Single Ended 90 Degree, 8-Wire, 10A 600V AC, PE Wire Code, 10' Length, Stainless Hex Nuts

Features

- Linkosity
- Cordset
- Male
- Single Ended 90 Degree

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Strands Multi
Number Of Conductors 8-Pole

Current

Amperage Rating 10 A

Voltage Rating 600V kV

Dimensions

Outside Diameter 0.81

General

Plug Type Linkosity
OEM Brand Name Hubbell Wiring Device-Kellems
UPC 783585243412
Color Gray

Logistics

Carton Quantity 10

Operational

Temperature Rating -20 Deg C to 105 Deg C

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)