

## Control Connectors, LINKOSITY, Right Angle Male Plug, 20A 8-Pole, 15' Cable Length.

By Hubbell Wiring Device-Kellems  
Catalog # [PN1008PE015](#)

Control Connectors, LINKOSITY, Right Angle Male Plug, 20A 8-Pole, 15' Cable Length.



### Features

- LINKOSITY
- Right Angle Male Plug
- 20A 8-Pole
- 15' Cable Length.

### Application

Quick Connect/Disconnect Signal and Control

### Specifications

EU RoHS Indicator Yes

### Conductor

Conductor Type Copper  
Strands Multi  
Number Of Conductors 8-Pole

### Current

Amperage Rating 10 A

Voltage Rating 600V kV

### Dimensions

Outside Diameter 0.81

### General

Plug Type Linkosity  
OEM Brand Name Hubbell Wiring Device-Kellems  
UPC 783585128306  
Color Gray

### Logistics

Carton Quantity 10

### Operational

Temperature Rating -20 Deg C to 105 Deg C

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)