

Signal And Control, Linkosity, Cordset, Male, Single Ended 90 Degree, 4-Wire, 20A 600V AC, PA Wire Code, 5' Length

By Hubbell Wiring Device-Kellems
Catalog # [PN2004PA005](#)

Signal And Control, Linkosity, Cordset, Male, Single Ended 90 Degree, 4-Wire, 20A 600V AC, PA Wire Code, 5' Length



Features

- Linkosity
- Cordset
- Male
- Single Ended 90 Degree

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator No

Conductor

Conductor Type Copper
Number Of Conductors 4-Pole

Dimensions

Diameter Live Part .46"

General

Jacket PVC
OEM Brand Name Hubbell Wiring Device-Kellems
UPC 783585192970
Color Gray

Logistics

Carton Quantity 10

Operational

Temperature Rating -20 Deg C to 105 Deg C

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)