

## Signal And Control, Linkosity, Cordset, Male, Single Ended 90 Degree, 5-Wire, 20A 600V AC, PA Wire Code, 10' Length

By Hubbell Wiring Device-Kellems  
Catalog # [PN2005PA010](#)

Signal And Control, Linkosity, Cordset, Male, Single Ended 90 Degree, 5-Wire, 20A 600V AC, PA Wire Code, 10' Length



### Features

- Linkosity
- Cordset
- Male
- Single Ended 90 Degree

### Application

Quick Connect/Disconnect Signal and Control

### Specifications

EU RoHS Indicator Yes

### Conductor

Conductor Type Copper  
Strands Multi  
Number Of Conductors 5-Pole

### Current

Amperage Rating 20 A

Voltage Rating 600V kV

### Dimensions

Outside Diameter 0.75

### General

Plug Type Linkosity  
OEM Brand Name Hubbell Wiring Device-Kellems  
UPC 783585243030  
Color Gray

### Logistics

Carton Quantity 10

### Operational

Temperature Rating -20 Deg C to 105 Deg C

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)