

Linkosity, 20A Single, Male, Right Angle Cable, 5'

By Hubbell Wiring Device-Kellems
Catalog # [PN2304PB005](#)

Linkosity, 20A Single, Male, Right Angle Cable, 5'



Features

- Linkosity
- 20A Single
- Male
- Right Angle Cable
- 5'

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Strands Multi
Number Of Conductors 4-Pole

Current

Amperage Rating 20 A

Voltage Rating 600V kV

Dimensions

Outside Diameter 0.75

General

Plug Type Linkosity
OEM Brand Name Hubbell Wiring Device-Kellems
UPC 783585116945
Color Gray

Logistics

Carton Quantity 10

Operational

Temperature Rating -20 Deg C to 105 Deg C

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)