

## Linkosity, Double Ended Female Right Angle Cable, 4-Wire, 10A, 10' Cable.

By Hubbell Wiring Device-Kellems  
Catalog # [PQ2304PB010](#)

Linkosity, Double Ended Female Right Angle Cable, 4-Wire, 10A, 10' Cable.



### Features

- Linkosity
- Double Ended Female Right Angle Cable
- 4-Wire
- 10A
- 10' Cable.

### Application

Quick Connect/Disconnect Signal and Control

### Specifications

EU RoHS Indicator Yes

### Conductor

Conductor Type Copper  
Strands Multi  
Number Of Conductors 4-Pole

### Current

Amperage Rating 20 A

Voltage Rating 600V kV

### Dimensions

Outside Diameter 0.75

### General

Plug Type Linkosity  
OEM Brand Name Hubbell Wiring Device-Kellems  
UPC 783585128214  
Color Gray

### Logistics

Carton Quantity 10

### Operational

Temperature Rating -20 Deg C to 105 Deg C

### Product Assets

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)