

Signal And Control, Linkosity, Cordset, Female, Double Ended, 90 Degree, 6-Wire, 20A 600V AC, PB Wire Code, 10' Length

By Hubbell Wiring Device-Kellems
Catalog # [PQ2306PB010](#)

Signal And Control, Linkosity, Cordset, Female, Double Ended, 90 Degree, 6-Wire, 20A 600V AC, PB Wire Code, 10' Length



Features

- Linkosity
- Cordset
- Female
- Double Ended

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Strands Multi
Number Of Conductors 6-Pole

Current

Amperage Rating 20 A

Voltage Rating 600V kV

Dimensions

Outside Diameter 0.77

General

Plug Type Linkosity
OEM Brand Name Hubbell Wiring Device-Kellems
UPC 783585128023
Color Gray

Logistics

Carton Quantity 5

Operational

Temperature Rating -20 Deg C to 105 Deg C

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)