

Signal And Control, Linkosity, Cordset, Double Ended Cable, 2) 90 Degree Fittings, 4-Wire, 10A 600V AC, PE Wire Code, 50' Length

By Hubbell Wiring Device-Kellems
Catalog # [PS1012PE050](#)

Signal And Control, Linkosity, Cordset, Double Ended Cable, 2) 90 Degree Fittings, 4-Wire, 10A 600V AC, PE Wire Code, 50' Length



Features

- Linkosity
- Cordset
- Double Ended Cable
- 2) 90 Degree Fittings

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Strands Multi
Number Of Conductors 12-Pole

Current

Amperage Rating 7 A

Voltage Rating 600V kV

Dimensions

Outside Diameter 0.89

General

Plug Type Linkosity
OEM Brand Name Hubbell Wiring Device-Kellems
UPC 783585131092
Color Gray

Logistics

Carton Quantity 5

Operational

Temperature Rating -20 Deg C to 105 Deg C

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)