

## Linkosity, 20A Single, Male Female Right Angle Cable, 15'

By Hubbell Wiring Device-Kellems  
Catalog # [PS2304PB015](#)



Linkosity, 20A Single, Male Female Right Angle Cable, 15'

### Features

- Linkosity
- 20A Single
- Male Female Right Angle Cable
- 15'

### Application

Quick Connect/Disconnect Signal and Control

### Specifications

EU RoHS Indicator Yes

### Conductor

Conductor Type Copper  
Strands Multi  
Number Of Conductors 4-Pole

### Current

Amperage Rating 20 A

Voltage Rating 600V kV

### Dimensions

Outside Diameter 0.75

### General

Plug Type Linkosity  
OEM Brand Name Hubbell Wiring Device-Kellems  
UPC 783585116846  
Color Gray

### Logistics

Carton Quantity 5

### Operational

Temperature Rating -20 Deg C to 105 Deg C

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)