

## Linkosity, 30A Male Female Right Angle Cable, 5'

By Hubbell Wiring Device-Kellems  
Catalog # [PS3004PA005](#)



Linkosity, 30A Male Female Right Angle Cable, 5'

### Features

- Linkosity
- 30A Male Female Right Angle Cable
- 5'

### Application

Quick Connect/Disconnect Signal and Control

### Specifications

EU RoHS Indicator Yes

### Conductor

Conductor Type Copper  
Strands Multi  
Number Of Conductors 4-Pole

### Current

Amperage Rating 30 A  
Voltage Rating 600V kV

### Dimensions

Outside Diameter 0.75

### General

Plug Type Linkosity  
OEM Brand Name Hubbell Wiring Device-Kellems  
UPC 783585116853  
Color Gray

### Logistics

Carton Quantity 10

### Operational

Temperature Rating -20 Deg C to 105 Deg C

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)