

Signal And Control, Linkosity, Cordset,
Double Ended Cable, 2) 90 Degree
Fittings, 4-Wire, 30A 600V AC, PB Wire
Code, 10' Length

By Hubbell Wiring Device-Kellems
Catalog # [PS3004PB010](#)

Signal And Control, Linkosity, Cordset, Double Ended Cable, 2)
90 Degree Fittings, 4-Wire, 30A 600V AC, PB Wire Code, 10'
Length

Features

- Linkosity
- Cordset
- Double Ended Cable
- 2) 90 Degree Fittings

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Strands Multi
Number Of Conductors 4-Pole

Current

Amperage Rating 30 A



Voltage Rating 600V kV

Dimensions

Outside Diameter 0.75

General

Plug Type Linkosity
OEM Brand Name Hubbell Wiring Device-Kellems
UPC 783585128054
Color Gray

Logistics

Carton Quantity 5

Operational

Temperature Rating -20 Deg C to 105 Deg C

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)