

## Signal And Control, Linkosity, Cordset, Double Ended Cable, 2) 90 Degree Fittings, 4-Wire, 40A 600V AC, PB Wire Code, 40' Length

By Hubbell Wiring Device-Kellems  
Catalog # [PS3004PB040](#)

Signal And Control, Linkosity, Cordset, Double Ended Cable, 2)  
90 Degree Fittings, 4-Wire, 40A 600V AC, PB Wire Code, 40'  
Length



### Features

- Linkosity
- Cordset
- Double Ended Cable
- 2) 90 Degree Fittings

### Application

Quick Connect/Disconnect Signal and Control

### Specifications

EU RoHS Indicator No

### Conductor

Conductor Type Copper  
Strands Multi  
Number Of Conductors 4-Pole

### Current

Amperage Rating 30 A

Voltage Rating 600V kV

### Dimensions

Outside Diameter 0.75

### General

Plug Type Linkosity  
OEM Brand Name Hubbell Wiring Device-Kellems  
UPC 783585454078  
Color Gray

### Logistics

Carton Quantity 5

### Operational

Temperature Rating -20 Deg C to 105 Deg C

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)