

Combination Devices, Residential Grade, 1) Single Pole Toggle, 1) Three Way Toggle, 15A 120V AC, Self Grounding, Side Wired

By Hubbell Wiring Device-Kellems
Catalog # [RC103AL](#)

Switches and Lighting Controls, Combination Devices,
Residential Grade, 1) Single Pole Toggle, 1) Three Way Toggle, 15A
120V AC, Self Grounding, Side Wired, Almond

Features

- Quiet snap action mechanism
- Self-grounding staple is standard
- Elongated strap with continuous plaster ears

Application

Residential

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Contact Manufacturer

Conductor

Number Of Poles	1) Single Pole, 1) Three Way
-----------------	------------------------------

Configuration

Contact Configuration	Two Position
-----------------------	--------------

Current

Current Rating	15 A
Amperage Rating	15 A
Current / Amperage Rating	15 A
Connectivity	Side Wired
Contact Rating	15A



Wattage	1800
Voltage Rating	120 VAC

Dimensions

Display Size	Standard Size
--------------	---------------

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Item Type	Traditional Switch Combo Devices
Material - Mounting Hardware	Mounting Screws
UPC	883778109928

Logistics

Carton Quantity	10
-----------------	----

Operational

Action	Snap Switch
Actuator	Toggle
Operating Cycles	30,000 Minimum
Operating Temperature	Max Continuous- 60 Degrees C, Minimum- -20 Without Impact

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)