

Combination Devices, Residential Grade, 1) Single Pole Toggle, 1) Single Tamper Resistant Receptacle, 15A 120V AC, Self Grounding, Side Wired

By Hubbell Wiring Device-Kellems
Catalog # [RC108ALTR](#)

Switches and Lighting Controls, Combination Devices,
Residential Grade, 1) Single Pole Toggle, 1) Single Tamper
Resistant Receptacle, 15A 120V AC, Self Grounding, Side Wired

Features

- Quiet snap action mechanism
- Self-grounding staple is standard
- Elongated strap with continuous plaster ears

Application

Residential

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes

Conductor

Number Of Poles	1) Single Pole
-----------------	----------------

Configuration

Contact Configuration	Two Position
-----------------------	--------------

Current

Current Rating	15 A
Amperage Rating	15 A
Current / Amperage Rating	15 A
Connectivity	Side Wired
Contact Rating	15A



Wattage	1800
Voltage Rating	120 VAC

Dimensions

Display Size	Standard Size
--------------	---------------

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Item Type	Traditional Switch and Receptacle Combo Devices
Material - Mounting Hardware	Mounting Screws
UPC	883778302237

Logistics

Carton Quantity	10
-----------------	----

Operational

Action	Snap Switch
Actuator	Toggle
Operating Cycles	30,000 Minimum
Operating Temperature	Max Continuous- 60 Degrees C, Minimum- -20 Without Impact

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)