

## Combination Devices, Residential Grade, 1) Three Way Toggle, 1) Single Receptacle, 15A 120V AC, Self Grounding, Side Wired

By Hubbell Wiring Device-Kellems  
Catalog # [RC308AL](#)

Switches and Lighting Controls, Combination Devices,  
Residential Grade, 1) Three Way Toggle, 1) Single Receptacle, 15A  
120V AC, Self Grounding, Side Wired, Almond



### Features

- Quiet snap action mechanism
- Self-grounding staple is standard
- Elongated strap with continuous plaster ears

### Application

Residential

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Contact Manufacturer

### Conductor

Number Of Poles	1) Three Way
-----------------	--------------

### Configuration

Contact Configuration	Two Position
-----------------------	--------------

### Current

Current Rating	15 A
Amperage Rating	15 A
Current / Amperage Rating	15 A
Connectivity	Side Wired
Contact Rating	15A

Wattage	1800
Voltage Rating	120 VAC

### Dimensions

Display Size	Standard Size
--------------	---------------

### General

OEM Brand Name	Hubbell Wiring Device-Kellems
Item Type	Traditional Switch and Receptacle Combo Devices
Material - Mounting Hardware	Mounting Screws
UPC	883778109867

### Logistics

Carton Quantity	10
-----------------	----

### Operational

Action	Snap Switch
Actuator	Toggle
Operating Cycles	30,000 Minimum
Operating Temperature	Max Continuous- 60 Degrees C, Minimum- -20 Without Impact

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[Spanish, French, English\]](#)