



Combination Devices, Residential Grade, 1) Three Way Toggle, 1) Single Tamper Resistant Receptacle, 15A 120V AC , Self Grounding, Side Wired

By Bryant
Catalog # [RC308ALTR](#)



Switches and Lighting Controls, Combination Devices,
Residential Grade, 1) Three Way Toggle, 1) Single Tamper
Resistant Receptacle, 15A 120V AC , Self Grounding, Side Wired

Features

- Residential Grade
- 1) Three Way Toggle
- 1) Single Tamper Resistant Receptacle
- 15A 120V AC
- Self Grounding

Application

Residential

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes

Conductor

Number Of Poles	1) Three Way
-----------------	--------------

Configuration

Contact Configuration	Two Position
-----------------------	--------------

Current

Current / Amperage Rating	15 A
Connectivity	Side Wired

Current Rating	15 A
Contact Rating	15A
Amperage Rating	15 A
Wattage	1800
Voltage Rating	120 VAC

Dimensions

Display Size	Standard Size
--------------	---------------

General

Item Type	Traditional Switch and Receptacle Combo Devices
Material - Mounting Hardware	Mounting Screws
UPC	883778302282

Logistics

Carton Quantity	10
-----------------	----

Operational

Operating Cycles	30,000 Minimum
Operating Temperature	Max Continuous- 60 Degrees C, Minimum- -20 Without Impact
Action	Snap Switch
Actuator	Toggle