



# Combination Devices, Residential Grade, Decorator Series, 1) Three Way Rocker, 1) Single Receptacle, 15A 120V AC, Side Wired

By Bryant  
Catalog # [RCD308BK](#)



Switches and Lighting Controls, Combination Devices, Residential Grade, Decorator Series, 1) Three Way Rocker, 1) Single Receptacle, 15A 120V AC, Side Wired, Black

## Features

- Smooth, quiet rocker
- Low profile, less than 1 inch deep
- Self-grounding feature is standard

## Application

Residential

## Performance

Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute, Electrical - Endurance - 30,000 cycles minimum, Electrical - Max. working voltage - 120V, Electrical - Overload - 1.5 times rating, Environmental - Flammability - UL V0, Environmental - Operating temperatures - Maximum continuous 60°C, minimum -20°C (without impact), Mechanical - Terminal accommodation - Back and side wire: #14 AWG min. - #12 AWG max. solid and stranded copper wire only, push wire: #14 AWG solid copper wire only

## Specifications

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified</li> <li>• UL Listed E3896</li> </ul>
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes

## Conductor

Number Of Poles	1) Three Way
-----------------	--------------

## Configuration

Contact Configuration	Two Position
-----------------------	--------------

## Current

Current / Amperage Rating	15 A
Connectivity	Side Wired

Current Rating	15 A
Contact Rating	15A
Amperage Rating	15 A
Voltage Rating Description	125 VAC
Wattage	1875
Voltage Rating	125 VAC

## Dimensions

Display Size	Standard Size
--------------	---------------

## General

Item Type	Decorator Switch and Receptacle Combo Devices
Material - Mounting Hardware Specifications	Mounting Screws <ul style="list-style-type: none"> <li>• Base and body - PVC</li> <li>• Mounting strap - Galvanized steel</li> <li>• Rocker - Polycarbonate</li> <li>• Terminal screws - Steel</li> <li>• Terminals - Brass</li> </ul>
UPC	883778110597

## Logistics

Carton Quantity	10
-----------------	----

## Operational

Operating Cycles	30,000 Minimum
Operating Temperature	Max Continuous- 60 Degrees C, Minimum- -20 Without Impact
Action	Snap Switch
Actuator	Rocker

## Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)