

Features

- Provides manual control of the room controller
- Connects to room controller using standard UTP RJ45 patchcords
- Predetermined configuration eliminates setup


Ordering Information

Description	Device Color	UPC Number	Catalog Number
2-Button; 1"ON", 1 "OFF"	Gray	783585564692	RCSNFGY



Specifications

Housing	Rugged, high-impact, injection-molded plastic
Dimensions	4.2" L x 1.60" W x 1.40" D



Performance

Electrical

Addressing	8-position rotary switch
Power Requirements	24V DC

Environmental

Operating Location	Indoor Use Only
Operating Temperature	0° to 40°C (32° to 104°F) Relative Humidity (non-condensing) 0% to 95%

Complementary Products

Wallplate	NPS26GY
Wallplate, Decorator Opening, Snap-on	NPS26GY
Wallplate, Decorator Opening, Stainless Steel	SS26
Patch cord	NSC5EY25PNB

Online Resources

eCatalog