

HUBBELL Premise Wiring

15A Kitchen Counter Receptacle, Surface Mount, Black

By Hubbell Premise Wiring
Catalog # [RCT200BK](#)

15A Kitchen Counter Receptacle, Surface Mount, Black



Features

- Spill water tested
- UL Listed for countertop installation.
- Permanent installation ready (suitable for MC cable or non-metallic sheath cable)
- Push down to pop-up function is rated for a minimum of 10,000 cycles
- Easy installations - simply drop in and tighten.

Specifications

EU RoHS Indicator	Contact Manufacturer
Nema Rating	5-15R

Conductor

Number Of Wires	3
Number Of Poles	2

Current

Current / Amperage Rating	15 A
Voltage Rating Description	125 V

Dimensions

Width	4.20 in
Height	6.48 in
Length	4.20 in
Dimensions	4.20 in x 4.20 in x 6.48 in

General

Type	Power Only
Series	Countertop Receptacle
UPC	883778307928
Style	Surface
Color	Black

Logistics

Carton Quantity	10
Pallet Quantity	480

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[French, English\]](#)